

**EURO CHLOR**  
**Bellows Sealed Globe Valve**

**EC11.35-G-FL-TT**




according to EURO CHLOR GEST 89/140

Certificate no. 08/02

<b>DN 65 - 350</b>	
<b>PN 40</b>	
Low temperature steel	
<b>Tmin.</b>	<b>- 40°C</b>
<b>Tmax.</b>	<b>+120°C</b>

Component	Material
	Low temp. steel
	<i>EC11.35-G-FL-TT</i>
Body	1.1138
Body seat	Stellite 21
Bonnet	1.1138
Disc	1.4571
Disc surface	Stellite 6
Bellows	2.4819
Bonnet gasket	1.4571/PTFE
Stud bolts	1.7225
Nuts	1.7218
Gland packing	PTFE
Gland follower	1.4408
O-Ring	Viton
Stem-upper part	1.4122
Stem-lower part	1.4571
Handwheel	0.6020

Flanges acc. DIN EN 1092-1				
DN	L [mm]	H <sub>open</sub> [mm]	D1 [mm]	G [kg]
65*	290	**	200	26
80	310	690	300	40
100	350	690	300	56
125*	400	**	300	86
150	480	1055	600	155
200*	600	**	600	255
250*	730	**	600	393
300*	850	**	600	492
350*	980	**	600	800



\* These sizes are not included in GEST 89/140.  
 Construction and materials are in conformity  
 with GEST 89/140.

\*\* available on request

**EURO CHLOR**  
**Bellows Sealed Globe Valve**

**EC11.35-G-FL-TT**



**according to EURO CHLOR GEST 89/140**

**Certificate no. 08/02**

Bellows Sealed Globe Valve **according to EURO CHLOR recommendation GEST 89/140**; straight type with flanges acc. EN 1092-1 for use on liquid and dry gaseous chlorine service and similar toxic, aggressive and corrosive media.

**Construction characteristics:**

- Bonnet flange in tongue and grooved design; bolting by stud bolts, with a nut at each end; bonnet gasket made of 1.4571 with PTFE coating.
- In- and outlet flanges securely bolted with blank flanges and fitted with suitable gaskets.
- Bellows anti-torque device with integrated position indicator for open and closed positions.
- Safety gland packing made of PTFE-silk; gland follower with double O-ring seal to prevent ingress of water into the packing area.
- Protected multiple wall bellows made of 2.4819/Hastelloy C276, designed for 20.000 operations, installed beyond main flow area.
- Body made of cast material 1.1138, seat hardfaced with stellite 21.
- Disc with conical plug made of s.s. 1.4571, sealing surface hardfaced with stellite 6.

**Testing / Marking:**

- Tests and design acc. to EURO CHLOR recommendation GEST 89/140, GEST 86/128, GEST 86/129.
- Quality level 3 of ASTM E446 or equivalent standard for body and bonnet.
- TÜV type test approval to VdTÜV 1065 available.
- Standard tests to DIN 3230 Part 3, resistance and leak test acc. to item BA/BQ.
- Leak test on closure acc. to item BO/BN (Leakage rate 1 = tight).
- TÜV approved strength calculations acc. to DIN 3840 available for body and bonnet.

**Preservation after manufacture and final tests**

- Drying at a temperature of 120°C (248°F) for at least 3 hours.
- Introducing of drying agents (Silicagel) into the valve.
- Blanking of inlet and outlet orifice with suitable gaskets and bolted flanges to avoid entry of moisture into the valve.
- Disc secured in closed position.
- Unfinished surfaces protected against rust.
- Lubrication with chlorofluorinated grease.